Temperature Controller

PTC10—*Programmable temperature controller*



- Up to 16 input channels
- Up to 4 PID feedback control channels
- 50 Hz PID sampling
- 1 mK resolution
- Data logging on removeable flash media
- USB, Ethernet, RS-232 interfaces (std.)
- GPIB interface (opt.)

PTC10 Temperature Controller

Introducing the PTC10 Programmable Temperature Controller from SRS — the ideal instrument for measuring temperature, controlling heaters, and logging temperature data.

The PTC10 Programmable Temperature Controller is a modular system that can be configured to suit a wide range of applications. The system consists of the PTC10 Controller and up to four I/O cards — two types of input cards for RTDs and thermocouples, and two types of output cards for controlling heaters. The I/O cards are ordered separately, and you can mix and match them in any way you wish.

Input Cards

The PTC321 input card supports up to four Pt RTD sensors. Each channel has a four-wire input with its own 1 mA current source for sensor excitation. The current can be reversed with each reading to cancel out stray thermocouple EMFs.

For thermocouples, the PTC330 four channel thermocouple input card should be used. It is factory configured to interface with either E, J, K or T type thermocouples. Each channel is electrically isolated allowing thermocouples to be attached to electrically-live equipment.

Both input cards have selectable low-pass filters that help reduce noise and improve PID feedback performance.

www.gmp.ch

GMP SAMain office: Avenue des Baumettes 17CH -1020 RenensTél. 021 633 21 21Fax. 021 633 21 29info@gmp.chGMP SABüro Zürich: Dübendorfstrasse 11aCH-8117 FällandenTel. 044 825 34 00Fax. 044 825 34 01info@gmp.ch





PTC330 Thermocouple card

PTC321 Pt RTD card

Output Cards

The PTC420 output card is a 120/240 VAC heater driver that delivers up to 5 A of current, and is intended to drive large heaters. Alternatively, the PTC430 DC output card delivers up to 50 VDC and 1 A of current for driving smaller heaters.





PTC420 AC output card

PTC430 DC output card

PID Feedback

Each output card is supported with a digital PID controller algorithm with automatic as well as manual tuning capability. You can servo PID controllers to any of the input signals, or the difference of any two input signals.

Since the temperature of most heaters is proportional to the square of the heater current or voltage, a square root filter is available to linearize the PID output.

Up to ten unique temperature ranges can be programmed with their own PID parameters.

Data Acquisition and Display

All temperature input channels are read simultaneously at a sampling rate that can be set between 1 Hz and 50 Hz. Temperature data can be displayed numerically or graphically

on the LCD display. A group of channels can be plotted on the same graph or on smaller individual graphs.

Alarms

Upper and lower alarm levels, or rate-of-change limits, can be assigned to each input channel. If these limits are exceeded, an audible alarm sounds, and assigned relays change state.

Programmability

Remote operation is supported with GPIB (opt.), RS-232 and Ethernet computer interfaces. All instrument functions can be controlled and read over any of the interfaces.

The PTC10 stores data on USB devices like flash keys, flash card readers, and USB hard drives. Data is stored in binary format to minimize file size and access time, but can be converted to ASCII text using an included application.

Multi-Purpose Ports

The PTC10 also has four configurable general purpose DACs/ADCs, eight bidirectional digital lines, and four relays. This can be replaced by the PTC332 single slot Pt RTD input card in case four output cards are needed in your application.

Flexibility

The PTC10 Programmable Temperature Controller has the flexibility to handle virtually any temperature control application. It's as useful in the research lab as it is in industry. The PTC10 is the right choice for all your temperature control experiments.



PTC322 Pt RTD card (single slot)



PTC10 rear panel

www.gmp.ch

GMP SAMain office: Avenue des Baumettes 17CH -1020 RenensTél. 021 633 21 21Fax. 021 633 21 29info@gmp.chGMP SABüro Zürich: Dübendorfstrasse 11aCH-8117 FällandenTel. 044 825 34 00Fax. 044 825 34 01info@gmp.ch

PTC10 Specifications

PTC10 Temperature Controller

Data acquisition rate	1 to 50 Hz		
Temperature resolution	<0.001 °C		
PID feedback	Both manual and auto-tuning		
	modes are available.		
Data display	320×240 pixel touchscreen.		
	Both numeric and graphical		
	data displays.		
Alarms	Upper and lower temperature		
	limits, and rate-of-change limits		
	can be set on each channel. If		
	exceeded, an audio alarm and a		
	relay closure will occur.		
Analog ports			
# of ports	4 configurable DAC or ADC ports		
Range	±10VDC		
Resolution	24-bit input, 16-bit output		
Update rate	50 Hz		
Connector	BNC		
Computer interface	USB, Ethernet, and RS-232.		
	GPIB (IEEE488.2) is optional.		
Power	10A		
	88 to 132 VAC or 176 to 264 VAC,		
	47 to 63 Hz or DC		
Dimensions	17"×5"×18" (WHL)		
Weight	25 lbs.		
Warranty	One years parts and labor on defects		
	in material and workmanship.		

PTC321 Pt RTD Card

Inputs

Noise

-200 °C to 550 °C Temperature range Four 100Ω Pt RTD 4-wire inputs Excitation 1 mA Accuracy $\pm 30 \,\mathrm{mK}$ 2 mKrms (10 samples/s) Temp. coefficient $1.4 \,\mathrm{mK/^{\circ}C}$ Signal conditioning Selectable 1 and 10 second time constant digital LPFs are provided. Card detects open and short circuit Signal detection conditions.

PTC330 Thermocouple Card

Thermocouple types E, J, K, or T Temperature range E-type J-type K-type T-type Inputs Input capacitance Connector type Accuracy Noise Temp. coefficient

−270 °C to 1000 °C
-210 °C to 1200 °C
−270 °C to 1370 °C
−270 °C to 400 °C
Four thermocouple inputs
<1 pF
Omega mini thermocouple jacks
±500 mK (over 12 months)
20 mKrms (10 samples/s)
20 mK/°C
(type K thermocouple at 164.0 K)

CMRR	100 dB
Common mode isolation	250 VAC

PTC420 AC Output Card

Output voltage Max. output current Cycle time Max. line voltage Surge current Output resolution Heater resistance (min.) 120/240 VAC 5A Adjustable between 1 and 240 s 250 VAC 100 A max. (non-repetitive) 0.1 % at 10 s cycle time $24 \Omega (110 \text{ VAC}), 46 \Omega (230 \text{ VAC})$

PTC430 DC Output Card

Max. output voltage	50 VDC
Voltage ranges	20 V and 50 V
Max. output current	1 A
Current ranges	0.1 A, 0.5 A, 1 A (50 V) or 2 A (20 V)
Output resolution	16-bit (24-bit with dithering)
Accuracy	±1 mA (1 A range)
	±0.1 mA (0.5 A range)
	±0.01 mA (0.1 A range)
Noise (rms), 25Ω load	$200\mu\text{V}$ (2 A range)
	15 µV (0.5 A range)
	$5 \mu V (0.1 A range)$

Ordering Information

PIC10	Programmable temperature controller
Opt.01	GPIB interface
PTC321	4-ch. Pt RTD card
PTC322	4-ch. Pt RTD card (single slot only)
PTC330J	4-ch. J-type thermocouple card
PTC330K	4-ch. K-type thermocouple card
PTC330E	4-ch. E-type thermocouple card
PTC330T	4-ch. T-type thermocouple card
PTC420	600 W AC output card
PTC430	50 W DC output card

www.gmp.ch

GMP SA	Main office: Avenue des Baumettes 17	CH -1020 Renens	Tél. 021 633 21 21	Fax. 021 633 21 29	info@gmp.ch
GMP SA	Büro Zürich: Dübendorfstrasse 11a	CH-8117 Fällanden	Tel. 044 825 34 00	Fax. 044 825 34 01	info@gmp.ch