Small Instrumentation Modules

SIM965 — Bessel and Butterworth filter

- Bessel and Butterworth filter types
- · 1 Hz to 500 kHz
- · 3-digit cutoff frequency resolution
- · High-pass or low-pass operation
- · Selectable rolloff
- Continuous time (not sampled)





SIM965 Analog Filter

The SIM965 Analog Filter is ideal for signal conditioning applications where Bessel or Butterworth filters are needed. Bessel filters offer clean step response (negligible overshoot) and linear phase response, while Butterworth filters provide excellent pass-band flatness with some overshoot. A choice of high-pass or low-pass filtering is selected from the front panel. Cutoff frequencies are set with 3-digit resolution, and a choice of 12, 24, 36 or 48 dB/octave rolloff is provided for either filter type.

The SIM965 accepts input signals between ±5 V, and has unity gain. Its low noise and low harmonic distortion, along with a bandwidth of greater than 1 MHz, make it ideal in sensitive analog applications. If signal amplification is needed, the SIM910 JFET Preamplifier, or the SIM911 BJT Preamplifier should be considered.

Up to eight SIM965 modules can be housed in one SIM900 mainframe. Mainframes can be cascaded, allowing an unlimited number of filter channels for complex applications.

The SIM965 is also fully programmable. All functions can be controlled from a computer via the SIM900 Mainframe. Both RS-232 and GPIB interfaces are supported by the mainframe.

The digital control circuitry in the SIM965 is designed with a special clock-stopping architecture in which the microcontroller is turned on only when settings are being changed. This guarantees that no digital noise can contaminate low-level analog signals.

Ordering Information

SIM965 Programmable analog filter

www.gmp.ch

GMP SA Main office: Avenue des Baumettes 17

CH -1020 Renens

Tél. 021 633 21 21

Fax. 021 633 21 29

info@gmp.ch

GMP SA Büro Zürich: Dübendorfstrasse 11a

CH-8117 Fällanden

Tel. 044 825 34 00

Fax. 044 825 34 01

info@gmp.ch

Input

 $\begin{array}{ll} \text{Impedance} & 1 \, \text{M}\Omega \\ \text{Coupling} & \text{AC or DC} \\ \text{Gain} & 1\times \\ \text{Max. input} & \pm 5 \, \text{V} \end{array}$

Filter

1 2

Filter Low-pass or high-pass Tuneable freq. range 1 Hz to 500 kHz

Resolution 3-digit

Type Butterworth, Bessel

Rolloff 12 dB/oct., 24 dB/oct., 36 dB/oct.,

or 48 dB/oct.

Output

Noise $<200\,\mu\text{Vrms}$ (1 MHz bandwidth) THD 0.01 % (80 dB) at 1 kHz

General

Operating temperature 0 °C to 40 °C, non-condensing Interface Serial via SIM interface

Connectors BNC (2 front, 1 rear)

DB15 (male) SIM interface Power +5 VDC (100 mA max.),

±15 VDC (300 mA max.)


Dimensions $1.5"\times3.6"\times7.0"$ (WHD)


Weight 1.5 lbs.

Warranty One year parts and labor on defects

in materials and workmanship


Step Response






Note: All graphs correspond to a 1 kHz cutoff frequency

Frequency Response





www.gmp.ch

GMP SA Main office: Avenue des Baumettes 17

GMP SA Büro Zürich: Dübendorfstrasse 11a

CH -1020 Renens

Tél. 021 633 21 21

Fax. 021 633 21 29

info@gmp.ch

CH-8117 Fällanden Tel. 044 825 34 00 Fax. 044 825 34 01 info@gmp.ch